


## Torica-sSY



on a scale of 5:1

## Technical Information

<b>Type</b>	Toric Posterior Chamber IOL with Blue Light Protection (Three-Piece, Foldable) for Sulcus Fixation
<b>Optic Material</b>	Silicone Elastomer with UV-Absorber and Yellow Colouring Agent
<b>Haptic Material</b>	High Molecular PMMA
<b>Haptic Shape</b>	Modified C-Loop
<b>Optic Shape</b>	Spheric Anterior Surface, Toric Posterior Surface
<b>Sphere Range</b>	in 0.5 D steps: 15.0 to 25.0 D in 1.0 D steps: -30.0 to 14.0 D / 26.0 to 34.0 D
<b>Cylinder Range</b>	in 0.5 D steps: 1.0 to 3.0 D in 1.0 D steps: 4.0 to max. 30.0 D*
	<b>Availability depending on combination of sphere and cylinder. More details on dioptric categories see page 2</b>
<b>A-Constant (est.)*</b>	118.0
<b>Cylinder Axis</b>	The Two Thin Diametrically Opposed Lines in the Periphery of the Optic Indicate the Axis of the Plus-Cylinder

## HumanOptics AG


Spardorferstraße 150  
91054 Erlangen

Phone: +49 (0) 9131 / 50665-0  
Fax: +49 (0) 9131 / 50665-90

www.humanoptics.com  
mail@humanoptics.com

03/2011

# Dioptr Category – Torica-sSY



The dioptr category does not indicate any conclusion related to availability. The delivery time of single powers might vary and is subject to change.